

ARTFORMA



User Manual
„Touch Clock“



Technical characteristics

The Touch Clock is a device that detects your touch thanks to a sandblasted pattern on the mirror that enables you to set 12-24h mode and a precise time. The Touch Clock is illuminated on white.



Specification

Current consumption:	1W
Tightness class:	IP20
Power supply:	12V DC
Dimensions:	112mm x 40mm



How to use it

1. After connection of power supply to the mirror, the clock will be illuminated on white.



2. If you would like to change clock settings, hold the switch for three seconds - the settings editor will open then. Enter changes by short pressing of the touch screen.







How to use it

3. First, set the format in which the time should be displayed. Choose the time format by fast pressing: 12- or 24-hrs.



4. Then hold the switch for three seconds to activate the time setting mode. Select the right time by short pressing. In order to set minutes, hold the switch down again for three seconds. Use short press in order to set minutes.





ARTFORMA

FORAM Sp. z o.o. sp. k.
Karpicko, ul. Podgórna 16, 64-200 Wolsztyn
NIP 923-172-93-78, REGON 381749814
Mail EU: info@artforma.eu; Mail PL: biuro@artforma.eu
+48 68 422 73 65

We work from Monday to Friday from: 9: 00 AM to 3. 00 PM